



### Liner Lock Selection Chart

Below is a list of current “Starfish” top discharge pumps, and the correct liner lock that will be used with our top only discharge bags.

| Manufacture          | Model                           | Dip Tube O.D.  | Compatible Bags                  | Arena Liner Lock |
|----------------------|---------------------------------|----------------|----------------------------------|------------------|
| <b>Standard Pump</b> | <b>SP-800-DD</b>                | 50mm (2")      | AP2320.1<br>AP2360.1<br>AP2360.2 | AP3098.1         |
|                      |                                 |                | AP2363.1<br>AP2363.2             | AP3098.2         |
| <b>Standard Pump</b> | <b>SP-800-SR</b>                | 50mm (2")      | AP2320.1<br>AP2360.1<br>AP2360.2 | AP3098.1         |
|                      |                                 |                | AP2363.1<br>AP2363.2             | AP3098.2         |
| <b>Flux</b>          | <b>F560 S3A-50/21</b>           | 50mm (2")      | AP2320.1<br>AP2360.1<br>AP2360.2 | AP3098.1         |
|                      |                                 |                | AP2363.1<br>AP2363.2             | AP3098.2         |
| <b>Flux</b>          | <b>F560 S3A-54/26</b>           | 54 mm (2.126") | AP2363.1<br>AP2363.2             | AP3098.5         |
| <b>Graco</b>         | <b>Saniforce 6:1<br/>24F942</b> | 54 mm (2.126") | AP2363.1<br>AP2363.2             | AP3098.5         |